




10-0185 - Surelite[™] Electronic Ballast

Specifications _

Model Number:	10-0185
Input Voltage:	120v AC
Frequency:	50/60 Hz
Designed for:	G15T8 / G30T8
Size:	6.5 x 1.5 x 1.0
Weight:	10 oz
Mounting:	Slotted Mounting Tabs





The information and recommendations contained in this publication are based upon data collected by the Atlantic Ultraviolet Corporation[®] and are believed to be correct. However, no guarantee or warranty of any kind, expressed or implied, is made with respect to the information contained herein. Specifications and information are subject to change without notice.


375 Marcus Boulevard • Hauppauge, NY 11788 • USA • 631.273.0500 • Fax: 631.273.0771 • e-mail: info@ultraviolet.com • ultraviolet.com • buyultraviolet.com Document No. 98-1680 • August 2017 • ©2017 by Atlantic Ultraviolet Corporation®





10-0185 - Surelite[™] Electronic Ballast

Connections.




Ground case in accordance with the National Electric Code. Cap and insulate any unused red wire individually.

Operates preheat lamps G15T8 or G30T8.

Wiring Jumper Detail

For Medium Bipin Lamps, add jumper between socket contacts, of the lampholder, before connecting the RED and YELLOW wires.



For 4-Pin Lamp Connections, Contact Factory

The information and recommendations contained in this publication are based upon data collected by the Atlantic Ultraviolet Corporation[®] and are believed to be correct. However, no guarantee or warranty of any kind, expressed or implied, is made with respect to the information contained herein. Specifications and information are subject to change without notice.